

# DRIVE DOWN COSTS WITH HI-SHOCK

Sumitomo Drive Technologies



## ***Mobil SHC™ Gear Hi-Shock 150***

After 5 years of testing in both the laboratory and the field, **ExxonMobil**, in partnership with Sumitomo Machine Corp. of America have formulated a unique, high-performance synthetic lubricant, Hi-Shock 150.

The revolutionary formulation significantly reduces internal friction, substantially extending operational life.

### ***Lower Total Cost of Ownership***

The exceptional oxidation resistance provides better lubrication, for longer, significantly extending service intervals.

### ***Enhanced Performance***


The radically different lubricant film properties provide a considerable increase in Cyclo® life.

### ***Full Synthetic***

The PAO based formula is compatible with both mineral oils and PAO synthetic oil, simplifying conversions.

### ***Three and Four Year Warranty***

Units shipped pre-filled are eligible for our extended warranty program. Contact your local SMA representative for details.



Lubrication failure is the most common limitation on Cyclo® life.


**Mobil SHC™ Hi-Shock 150 is the only synthetic oil approved by Sumitomo Drive Technologies for general use.**



## Sumitomo Drive Technologies

A global power transmission solutions provider. With facilities strategically located throughout the world, providing comprehensive products and services in your region.

### Headquarters



4200 Holland Blvd  
Chesapeake, VA 23323

email: [SMA.CustomerService@shi-g.com](mailto:SMA.CustomerService@shi-g.com)  
phone: 757-485-3355

- ★ MANUFACTURING HUB & HEADQUARTERS
- ★ MANUFACTURING HUB
- ASSEMBLY & SERVICE
- SERVICE
- ▲ REGIONAL SALES OFFICE